



K070

Busbar terminal 1,5mm<sup>2</sup>-16mm<sup>2</sup>, for 12x5mm busbars, for copper conductors

**Technical Features**

**Connection**

|                                  |                          |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 1.5 - 16 mm <sup>2</sup> |
| Cross-section rigid conductor    | 16 mm <sup>2</sup>       |

**Installation, mounting**

|                           |          |
|---------------------------|----------|
| Nominal tightening torque | 1 - 1 Nm |
|---------------------------|----------|

**Dimensions**

|                        |            |
|------------------------|------------|
| Height busbar          | 5 mm       |
| Width/thickness busbar | 12 - 12 mm |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 65 A |
|---------------|------|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |