



WXF432

Double socket with detrompage for trunking gallery 2P+E 16A

Technical Features

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Red
RAL code	3020
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Height	42.50 mm
Width	90 mm
Depth	45 mm
Number of units	2
Built-in depth flush-mounted boxes	50 mm

Installation, mounting

Mounting on	Wall duct
-------------	-----------

Connectivity

Mounting type	Click mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	French norm NF
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	4
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
Protection	Enhanced contact protection

Suitable for

gallery	
---------	--

Sustainability

Halogen free	Yes
RoHS conform	Yes
