



303650

Change-over switch for inst. in hollow walls, light control

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Surface finish Matt

Material Metal
Plastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 71 x 71 mm

Built-in depth 19.50 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Texts

Installation mode Low installation depth
For screw fastening
Without spreader claws

Type of connection With plug-in terminals

Lighting For lighting and monitoring circuit

Switch mode Off/change-over

Sustainability

Halogen free Yes

RoHS conform Yes