



47893525



**Double SCHUKO sock.outl. w. hing. cov., lab. field, diff. closure, W1 grey**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Use conditions**

Operating temperature -15 - 30 °C

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Grey  
RAL code 7011  
Surface finish Matt  
Material Thermoplastic  
Treatment Untreated

**Dimensions**

Height 80 mm  
Width 100.70 mm  
Depth 51 mm  
Number of units 2  
Height of P-touch band for labelling field 12 mm

**Connection**

Connector/plug type Plug-in terminal  
Conductor cross-section 1.0 - 2.5 mm<sup>2</sup>

**Installation, mounting**

Mounting on Surface mounting

**Connectivity**

Type of connection Plug-in connection  
Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO  
Rotated central insert No  
With hinged lid Yes  
With round protective earth pin No  
With signal lamp No  
With lock Yes

**Accessories**

Has labelling field Yes

**Cover, door**

Type of lid Self-closing hinged cover, can be arrested in end position

**Capacity**

Number of modules 2

**Safety**

With enhanced contact protection No  
Impact resistance IK IK05  
Ingress Protection (IP) class IP55

---

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With plug-in terminals
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor

**Sustainability**

Halogen free	Yes
RoHS conform	Yes