



47527209



SCHUKO soc. out. hinged cover, enhanced contact protection, K.1, p. white glossy

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth flush-mounted boxes 35 mm

Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid Yes

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field Yes

Cover, door

Type of lid Hinged cover falls back

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP44

Functions

With orientation lighting No

With function lighting No

Identification

With imprint	No
--------------	----

Texts

Cover	Central cover plate
-------	---------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Labelling	With labelling field
-----------	----------------------

Suitable for

K.x	
-----	--

Sustainability

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----
