



WXPDP84

**IP66 20A 1 Gang 1 Way Double Pole Switch**

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour Light grey

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

**Identification**

Assembly arrangement Basic element with complete housing

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 90 x 90 mm

Built-in depth 0 mm

**Safety**

Ingress Protection (IP) class IP66

**Architecture**

Control/operation element Single rocker

**Electric current**

Rated current 20 A

**Texts**

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes