Product Datasheet
WXPDP84



WXPDP84

IP66 20A 1 Gang 1 Way Double Pole Switch

Technical Features

Installation, mounting

Mounting on	Surface mounting

Voltage

Rated voltage	250 V

Materials

Colour	Light grey
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Basic element with complete housing

Connectivity

Mounting type	Screw mounting

Controls and indicators

Number of buttons	1

Dimensions

Dimensions	90 x 90 mm
Built-in depth	0 mm

Electric current

Rated current IN	20 A

Texts

Lighting	Without lighting (cannot be illuminated)
Push button	No
Imprint	With clear terminal markings

Architecture

Control/operation element	Single rocker

Sustainability

REACh-SVHC free	Yes