



VB218W

Small distributor, vega, surface, 2row, 36M, IP40, QC-terminal, PE, transparent door

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	90 A
---------------	------

Equipment

Number of rails	2
-----------------	---

Number of rows	2
----------------	---

With lock	No
-----------	----

Has neutral terminal block	No
----------------------------	----

Capacity

Number of modules	36
-------------------	----

Dimensions

Height	475 mm
--------	--------

Width	400 mm
-------	--------

Depth	146 mm
-------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Number of locks	1
-----------------	---

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Materials

Material	Polystyrene (PS)
----------	------------------

RAL code	9010
----------	------

Colour	White
--------	-------

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

Safety

Impact resistance IK	IK07
----------------------	------

Ingress Protection (IP) class	IP40
-------------------------------	------

Locking type	Snap on lock Without lock
--------------	------------------------------

Glow wire test	650 °C
----------------	--------

Sustainability

RoHS conform	Yes
--------------	-----