



HHA160Z

Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 160A 25kA CTC

Technical Features

Electric current

Rated current	160 A
Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	35 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2	20 kA
Rated current 10°C according to IEC 60947	187.20 A
Rated current 15°C according to IEC 60947	184 A
Rated current 20°C according to IEC 60947	180.70 A
Rated current 25°C according to IEC 60947	177.40 A
Rated current 30°C according to IEC 60947	174.10 A
Rated current at 35°C according to IEC 60947	170.70 A
Rated current at 40°C according to IEC 60947	167.20 A
Rated current 45°C according to IEC 60947	163.60 A
Rated current 50°C according to IEC 60947	160 A
Rated current 55°C according to IEC 60947	156.20 A
Rated current at 60°C according to IEC 60947	152.40 A
Rated current 65°C according to IEC 60947	148.50 A
Rated current 70°C according to IEC 60947	144.40 A

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	690 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Total power loss under I _N	43.80 W
---------------------------------------	---------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	4 - 70 mm ²
Cross-section rigid conductor	4 - 95 mm ²

Installation, mounting

Mounting-/Connection Position	Front
-------------------------------	-------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Settings	
Thermal protection knob setting xIN	1
	1
Dimensions	
Height	130 mm
Width	75 mm
Depth	68 mm
Compatibility	
Suitable for DIN Rail	No
Main electrical attributes	
Magnetic protection trip time	0 - 0 ms
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes