



VB218J

Small distributor,vega,surface,2row,36M,IP40,brass-terminal,PE,white door

Technical Features

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 90 A

Equipment

Number of rails 2
 Number of rows 2
 With lock No
 Has neutral terminal block No

Capacity

Number of modules 36

Dimensions

Height 475 mm
 Width 400 mm
 Depth 146 mm

Cover, door

Number of cabinet doors 1
 Number of locks 1

Dimensions

Number of width units 18

Cover, door

Door/cover is transparent No

Materials

Material Polystyrene (PS)
 RAL code 9010
 Colour White

Equipment

Has earthing terminal block Yes
 Has mounting plate No

Safety

Impact resistance IK IK07
 Ingress Protection (IP) class IP40
 Locking type Snap on lock
Without lock
 Glow wire test 650 °C

Sustainability

RoHS conform Yes