



Steel enclosure, Orion.Plus, plain door 650x400x250 mm

Technical Features

Cover, door

Door/cover is transparent	No
Number of cabinet doors	1
Number of locks	1

Dimensions

Depth	250 mm
Height	650 mm
Thickness of sidewall	1.2 mm
Width	400 mm

Electric current

Rated current	250 A
---------------	-------

Equipment

Number of flange plate openings	2
Number of rows	4
Number of section in width	0

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
Material	Steel
RAL code	7035
Treatment	Powder coated

Safety

Impact resistance IK	IK10
Ingress Protection (IP) class	IP65
Locking type	3-Side 7 mm Key lock
Protection class	Isolation class I

Sustainability

Halogen free	Yes
RoHS conform	Yes