



REA665X



Indoor station video comfort WM 2wire black shiny TOUCH

Technical Features

Materials

Colour	Black
RAL code	9005
Surface finish	Glossy
Material	Plastic Thermoplastic

Dimensions

Height	145 mm
Width	93 mm
Depth	16 mm
Dimensions	145 x 93 mm

Use conditions

Operating temperature	5 - 50 °C
Storage/transport temperature	-20 - 60 °C

Voltage

Operating voltage over bus	24 - 24 V
----------------------------	-----------

Electric current

Current consumption during operation	220 mA
Current consumption (idle)	12 mA

Screen

With touch screen	No
-------------------	----

Texts

Installation mode	Flat surface-mounted installation or onto wall box For vertical mounting
Junction	For floor call push-button For optional additional power supply Connection terminal block with screw terminals

Functions

Door communication type	Audio + Video
Volume control	Yes

Connection

Conductor cross-section	0 - 0 mm ²
-------------------------	-----------------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Accessories

Additional device connectable	No
-------------------------------	----