



WXF105

Socket gallery refurbishing 2P+E

Technical Features

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Height	45 mm
Width	45 mm
Depth	35.85 mm
Number of units	1
Built-in depth flush-mounted boxes	40 mm

Connectivity

Mounting type	Click mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	French norm NF
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP21

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Protection	Enhanced contact protection
------------	-----------------------------

Suitable for

gallery	
---------	--

Sustainability

Halogen free	Yes
RoHS conform	Yes
