



303808



Double change-over switch, isolated input terminals, light control

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Surface finish Matt

Material Metal
Plastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Claw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 71 x 71 mm

Built-in depth 31 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Impact resistance IK IK07

Architecture

Control/operation element Double rocker

Electric current

Rated current 10 A

Texts

Installation mode With spreader claws

Type of connection With screw terminals

Lighting For illumination

Switch mode Double off/change-over, isolated input terminals

Sustainability

RoHS conform Yes