

Product Datasheet

303808



303808



Double change-over switch, isolated input terminals, light control

Technical Features

Electric current	
Switching current	10 AX (100W LED (SBL))

Installation, mounting	
Mounting on	Flush mounting

Voltage	
Rated voltage	250 V

Frequency	
Frequency	50 - 60 Hz

Materials	
Surface finish	Matt
Material	Metal Plastic

Identification	
Assembly arrangement	Basic element

Connectivity	
Mounting type	Claw mounting

Controls and indicators	
Number of buttons	2

Dimensions	
Dimensions	71 x 71 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm

Safety	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Architecture	
Control/operation element	Double rocker

Electric current	
Rated current	10 A

Texts	
Installation mode	With spreader claws
Type of connection	With screw terminals
Lighting	For illumination
Switch mode	Double off/change-over, isolated input terminals

Sustainability	
RoHS conform	Yes