

Switch h1600 3P 1250A

Technical Features

Electric current

Rated current	1250 A
---------------	--------

Architecture

Number of poles	3
-----------------	---

Control/operation element	Toggle
---------------------------	--------

Connection

Cross-section rigid conductor	3x 240 mm ²
-------------------------------	------------------------

Cross-section flexible conductor	3x 240 mm ²
----------------------------------	------------------------

Voltage

Rated insulation voltage U _i	800 V
---	-------

Rated impulse withstand voltage U _{imp}	8000 V
--	--------

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Equipment

Motor drive optional	Yes
----------------------	-----

Functions

Trip unit	Switch
-----------	--------

Power

Power loss per pole at I _n	62.50 W
---------------------------------------	---------

Total power loss under I _N	187.50 W
---------------------------------------	----------

Rated operational power under 400 V AC AC1	822000 W
--	----------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Sustainability

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----