



HNGxxU-3P

Moulded Case Circuit Breaker h250 3P 50kA 250A TM

Technical Features

Electric current

Rated current	250 A
---------------	-------

Architecture

Number of poles	3
-----------------	---

Electric current

Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V

Functions

Trip unit	TM A/A
-----------	--------

Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

Power

Total power loss under IN	48.90 W
---------------------------	---------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²
Connector/plug type	Terminal

Installation, mounting

Nominal tightening torque	12 - 12 Nm
Mounting-/Connection Position	Front

Settings

Thermal protection knob setting xIN	0.63 0.8 1
Adjustment range short-term delayed short-circuit release	0 - 0 A

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes