



WXF251

**TV socket gallery passthrough BNC socket 10 db 2 modules**

**Technical Features**

**Capacity**

Number of gangs	1
Number of modules	2

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Attenuation**

Tap loss at 860 MHz	10 dB
Through loss 860 MHz	10 dB

**Connection**

Connector/plug type	Pass-through socket
---------------------	---------------------

**Frequency**

Frequency bandwidth	4 - 862 MHz
---------------------	-------------

**Equipment**

Number of outputs	1
-------------------	---

**Materials**

Material	Metal Plastic
Colour	Grey
RAL code	7011

**Dimensions**

Depth	34 mm
-------	-------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Identification**

Assembly arrangement	Middle plate
----------------------	--------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes