



47552089

SCHUKO soc.out.,enhncd contact prot.,mounting orient. var. in 45° steps,R.cl,wh

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Depth 42 mm

Number of units 1

Built-in depth flush-mounted boxes 31 mm

Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting

Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert Yes

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

R.x / Serie R.classic

Sustainability

Halogen free	Yes
RoHS conform	Yes