



WFDP84BSB

20A Double Pole Switch Brushed Steel Black Insert

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Stainless steel

Surface finish Matt

Material Stainless steel

Treatment Brushed

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 27.90 mm

Electric current

Rated current 20 A

Texts

Lighting Without lighting (cannot be illuminated)

Push button No

Imprint With clear terminal markings

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes