

Product Datasheet

SM102E



SM102E

Multi-function measurement device

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Height	96 mm
Width	96 mm
Depth	60 mm

Capacity

Number of modules	5
-------------------	---

Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	2.5 - 6 mm ²
Cross-section rigid conductor	2.5 - 6 mm ²

Power

Total power loss under IN	10 W
Power consumption VA	10 VA

Equipment

Type of display	LCD
-----------------	-----

Measurement

Frequency measuring range	45 - 65 Hz
Type of measuring instrument	Multimeter
Current measurement range	0 - 9999 A

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes