



HBW630H

### RCD add on P630 4P 630A Idn adj

#### Technical Features

##### Electric current

Rated current	630 A
Rated residual operating current Idn	100 mA
	300 mA
	500 mA
	1000 mA
	3000 mA
	10000 mA



#### Architecture

Number of poles	4
-----------------	---

#### Safety

Residual current type	A HI
-----------------------	------

#### Voltage

Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

#### Sustainability

RoHS conform	Yes
--------------	-----