




TYB602F



**Output module 2x 6A /230V~, flush mounted, KNX**

**Technical Features**

**Settings**

Supported configuration mode	ETS
------------------------------	-----

**Connectivity**

With bus system KNX	Yes
With bus system KNX radio	No

**Dimensions**

Dimensions	44 x 43 mm
Height	44 mm
Width	43 mm
Depth	22 mm
Built-in depth	40 mm

**Electric current**

Rated current	6 A
---------------	-----

**Materials**

Colour	Light grey
--------	------------

**Equipment**

Radio frequency bidirectional	No
With switch for manual switch	Yes

**Electric current**

Bus current consumption while idle	5 mA
------------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Output power	500 W
230 V incandescent and halogen lamp	500 W

**Voltage**

Rated operational voltage Ue	230 - 230 V
System supply voltage	30 V DC Via bus
Operating voltage over bus	21 - 32 V

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Connection**

Cross-section rigid conductor	0.75 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor	0.75 - 2.5 mm <sup>2</sup>

**Texts**

Function	With safety functions e.g. for wind, rain, alarm With positioning function for blind and lamella position With sun shade function
Type of connection	With screw terminals

**Sustainability**

RoHS conform	Yes
--------------	-----