

# Product Datasheet

## TYB601B



TYB601B



Output module 1x 10A /230V~, flush mounted, KNX

### Technical Features

#### Settings

Supported configuration mode ETS

#### Connectivity

With bus system KNX Yes

With bus system KNX radio No

#### Dimensions

Dimensions 44 x 43 mm

Height 44 mm

Width 43 mm

Depth 22 mm

Built-in depth 40 mm

#### Electric current

Rated current 10 A

#### Materials

Colour Light grey

#### Equipment

Radio frequency bidirectional No

With switch for manual switch Yes

#### Electric current

Bus current consumption while idle 5 mA

#### Frequency

Frequency 50 - 60 Hz

#### Power

Power incandescent lamp 230 V 600 - 600 W

Output power 500 W

230 V incandescent and halogen lamp 600 W

#### Voltage

Rated operational voltage U<sub>e</sub> 230 - 230 V

System supply voltage 30 V DC Via bus

Operating voltage over bus 21 - 32 V

#### Safety

Ingress Protection (IP) class IP20

#### Use conditions

Operating temperature -5 - 45 °C

#### Connection

Cross-section rigid conductor 0.75 - 2.5 mm<sup>2</sup>

Cross-section flexible conductor 0.75 - 2.5 mm<sup>2</sup>

#### Texts

Type of connection With screw terminals

#### Sustainability

RoHS conform Yes