



85421200

Universal touch dimmer 1gang, electronics

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Materials

Material Metal Plastic

Dimensions

Built-in depth 32 mm

Height 71 mm

Width 71 mm

Depth 33.20 mm

Architecture

Control/operation element Single push button

Power

Power consumption standby 0.30 W

Lighting

Dimmable 230 V LED lamp 5 - 70 W

Use conditions

Operating temperature -5 - 45 °C

Texts

Dimming principle Automatic setting of load-dependent switching principle (autodetect process)
Phase cut-on or cut-off according to load type, self-learning

Fuse Short-circuit and overload-proof (electronic fuse)

Installation mode With spreader claws

Type of connection With screw terminals

Extension unit input With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit

Sustainability

RoHS conform Yes