




WGML132

16AX 3G 2W switch

Technical Features

Electric current	
Switching current	16 A
Installation, mounting	
Mounting on	Flush mounting
Voltage	
Rated voltage	250 V
Materials	
Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Connectivity	
Mounting type	Screw mounting
Controls and indicators	
Number of buttons	3
Dimensions	
Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm
Safety	
Ingress Protection (IP) class	IP20
Architecture	
Control/operation element	Triple rocker
Electric current	
Rated current	16 A
Texts	
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way
Sustainability	
RoHS conform	Yes