



WGML142

### 16AX 4G 2W switch

#### Technical Features

##### Electric current

|                   |      |
|-------------------|------|
| Switching current | 16 A |
|-------------------|------|

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Materials

|                |                    |
|----------------|--------------------|
| Colour         | White              |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 4 |
|-------------------|---|

##### Dimensions

|                                    |            |
|------------------------------------|------------|
| Dimensions                         | 86 x 86 mm |
| Built-in depth flush-mounted boxes | 35 mm      |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | 4-gang rocker |
|---------------------------|---------------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Texts

|             |                                          |
|-------------|------------------------------------------|
| Lighting    | Without lighting (cannot be illuminated) |
| Switch mode | 2-way                                    |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|