



WGML112

16AX 1G 2W switch

Technical Features

Electric current

Switching current	16 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	16 A
---------------	------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes