



JK114AG

**JK A Board 1 Row Glazed Door**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Capacity**

Number of modules	14
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	107.70 mm
Height	300 mm
Width	465 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	Yes

**Materials**

RAL code	7035
Colour	Light grey
Material	Steel

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

Number of rows	1
With socket outlet	No

**Safety**

Ingress Protection (IP) class	IP30
Protection class	Isolation class I
Number of earth leakage switches 300 mA	0

**Sustainability**

RoHS conform	Yes
--------------	-----