



HBW630H



RCD add on P630 4P 630A I<sub>dn</sub> adj

Technical Features

Electric current

Rated current	630 A
Rated residual operating current I <sub>dn</sub>	100 mA
	300 mA
	500 mA
	1000 mA
	3000 mA
	10000 mA

Architecture

Number of poles	4
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Voltage

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	6000 V

Sustainability

RoHS conform	Yes
--------------	-----