



283410

Rot. dimmer centre plate (R, L, C), soft-lock, 1930/glass, p. white glossy

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Material Metal Plastic

Dimensions

Diameter axis 4 mm

Height 71 mm

Width 71 mm

Depth 61 mm

Architecture

Control/operation element Push & rotative switch

Use conditions

Operating temperature 5 - 25 °C

Texts

Dimming principle Phase cut-on or cut-off according to load type, self-learning

Fuse Short-circuit and overload-proof (electronic fuse)

Voltage Voltage test possible without dismantling

Installation mode For screw fastening

Type of connection With plug-in terminals

Extension unit input With input for extension units insert for universal rotary dimmer

Equipment

Substation input Yes

Sustainability

REACH-SVHC free Yes

RoHS conform Yes