



WXPPS22

IP66 10AX 2 Gang 2 Way Switch

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Light grey

Surface finish Matt

Material Polycarbonate (PC)

Treatment Untreated

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 90 x 90 mm

Safety

Ingress Protection (IP) class IP66

Architecture

Control/operation element Double rocker

Electric current

Rated current 10 A

Texts

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way

Sustainability

REACH-SVHC free Yes

RoHS conform Yes