



HBW400H

RCD add on P630 4P 400A I_{dn} adj

Technical Features

Electric current

Rated current I _N	400 A
Rated residual operating current I _{dn}	100 mA
	300 mA
	500 mA
	1000 mA
	3000 mA
	10000 mA

Architecture

Number of poles	4
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	6000 V

Sustainability

RoHS conform	Yes
--------------	-----