



JG220U

### IP66 20A 3P ISOLATOR

#### Technical Features

##### Architecture

Number of poles	3
Type of pole	3P

##### Electric current

Rated current	20 A
Acceptable current rating AC21	20 A
Acceptable current rating AC21 category A	20 A
Rated short-time withstand current I <sub>cs</sub> IEC 60947	0.24 kA
Acceptable current rating AC22 category A	20 A

##### Voltage

Rated operational voltage U <sub>e</sub>	380 - 440 V
--	-------------

##### Electric current

Acceptable current rating AC23 category A	20 A
---	------

##### Voltage

Rated insulation voltage U <sub>i</sub>	440 V
---	-------

##### Installation, mounting

Nominal tightening torque	2 - 2 Nm
---------------------------	----------

##### Dimensions

Height	170 mm
Width	84 mm
Depth	87 mm

##### Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

##### Power

Rated operational power under 400 V AC AC23	9900 W
---	--------

##### Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

##### Connection

Cross-section rigid conductor	2.5 - 4 mm <sup>2</sup>
-------------------------------	-------------------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Sustainability

RoHS conform	Yes
--------------	-----