



633023



**Rocker switch 3 x 1-pole Off, Module inserts**

**Technical Features**

**Electric current**

Switching current 16 AX (200W LED (SBL))

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 400 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Surface finish Matt  
Material Metal  
Plastic

**Identification**

Assembly arrangement Basic element

**Connectivity**

Mounting type Clamp mounting  
Screw connection

**Controls and indicators**

Number of buttons 3

**Dimensions**

Dimensions 71 x 71 mm  
Built-in depth 32 mm  
Built-in depth flush-mounted boxes 35 mm

**Safety**

Ingress Protection (IP) class IP20  
Impact resistance IK IK07

**Architecture**

Control/operation element Single rocker

**Electric current**

Rated current 16 A

**Texts**

Type of connection With screw terminals  
Lighting Can be illuminated using neon lamp, incandescent or LED unit with N terminal  
Switch mode 3x 1--pole off

**Sustainability**

RoHS conform Yes