



633023



Rocker switch 3 x 1-pole Off, Module inserts

Technical Features

Electric current	
Switching current	16 AX (200W LED (SBL))

Installation, mounting	
Mounting on	Flush mounting

Voltage	
Rated voltage	400 V

Frequency	
Frequency	50 - 60 Hz

Materials	
Surface finish	Matt
Material	Metal Plastic

Identification	
Assembly arrangement	Basic element

Connectivity	
Mounting type	Clamp mounting Screw connection

Controls and indicators	
Number of buttons	3

Dimensions	
Dimensions	71 x 71 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

Safety	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Architecture	
Control/operation element	Single rocker

Electric current	
Rated current	16 A

Texts	
Type of connection	With screw terminals
Lighting	Can be illuminated using neon lamp, incandescent or LED unit with N terminal
Switch mode	3x 1--pole off

Sustainability	
RoHS conform	Yes