



633023



Rocker switch 3 x 1-pole Off, Module inserts

Technical Features

Electric current

Switching current 16 AX (200W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 400 V

Frequency

Frequency 50 - 60 Hz

Materials

Surface finish Matt
Material Metal
Plastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Clamp mounting
Screw connection

Controls and indicators

Number of buttons 3

Dimensions

Dimensions 71 x 71 mm
Built-in depth 32 mm
Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20
Impact resistance IK IK07

Architecture

Control/operation element Single rocker

Electric current

Rated current 16 A

Texts

Type of connection With screw terminals
Lighting Can be illuminated using neon lamp, incandescent or LED unit with N terminal
Switch mode 3x 1--pole off

Sustainability

RoHS conform Yes