



633023



**Rocker switch 3 x 1-pole Off, Module inserts**

**Technical Features**

<b>Electric current</b>	
Switching current	16 AX (200W LED (SBL))

<b>Installation, mounting</b>	
Mounting on	Flush mounting

<b>Voltage</b>	
Rated voltage	400 V

<b>Frequency</b>	
Frequency	50 - 60 Hz

<b>Materials</b>	
Surface finish	Matt
Material	Metal Plastic

<b>Identification</b>	
Assembly arrangement	Basic element

<b>Connectivity</b>	
Mounting type	Clamp mounting Screw connection

<b>Controls and indicators</b>	
Number of buttons	3

<b>Dimensions</b>	
Dimensions	71 x 71 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

<b>Safety</b>	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

<b>Architecture</b>	
Control/operation element	Single rocker

<b>Electric current</b>	
Rated current	16 A

<b>Texts</b>	
Type of connection	With screw terminals
Lighting	Can be illuminated using neon lamp, incandescent or LED unit with N terminal
Switch mode	3x 1--pole off

<b>Sustainability</b>	
RoHS conform	Yes