




80262180



S.x KNX (TP+EASY) Movement detector module 1,10m

Technical Features

Dimensions

Recommended installation height	1.10 - 1.10 m
---------------------------------	---------------

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Minimal duty cycle

10 s

Functions

Maximal duty cycle	30 min
--------------------	--------

Connectivity

With bus system KNX radio	No
---------------------------	----

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Electric current

Bus current consumption data transfer	10 mA
---------------------------------------	-------

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Detection

Detection angle adjustable	45 - 90 °
----------------------------	-----------

Detection angle horizontal

90 - 180

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Material	Metal Plastic
----------	------------------

Texts

Push button	With button for automatic/permanent ON/permanent OFF
-------------	--

Operating mode	With test mode Master/slave operation for covering large detection areas With 3 operating modes: automatic/permanent ON/permanent OFF
----------------	---

Function

Presence simulation
With party function

Installation mode

With spreader claws
With dismantling protection