



53420212



Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 13 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour White
RAL code 1013
Surface finish Glossy
Material Thermoplastic
Treatment Untreated

Dimensions

Height 71 mm
Width 71 mm
Built-in depth flush-mounted boxes 40 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting

Equipment

Connector/plug type socket outlet British Standard
Rotated central insert No
With hinged lid No
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection No
Impact resistance IK IK02
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate
Protection Enhanced contact protection
Type of connection With screw terminals

Sustainability

RoHS conform

Yes