



53420212



Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

#### Technical Features

##### Voltage

Rated voltage 250 V

##### Electric current

Rated current 13 A

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Colour White

RAL code 1013

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

##### Dimensions

Height 71 mm

Width 71 mm

Built-in depth flush-mounted boxes 40 mm

##### Installation, mounting

Mounting on Flush mounting

##### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

##### Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

##### Accessories

Has labelling field No

##### Capacity

Number of modules 1

##### Safety

With enhanced contact protection No

Impact resistance IK IK02

Ingress Protection (IP) class IP20

##### Functions

With orientation lighting No

With function lighting No

##### Identification

With imprint No

##### Texts

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With screw terminals

---

**Sustainability**

---

RoHS conform

Yes