



53420212



Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 13 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

RAL code 1013

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Built-in depth flush-mounted boxes 40 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection No

Impact resistance IK IK02

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With screw terminals

Sustainability

RoHS conform

Yes