



53420216



Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

#### Technical Features

##### Voltage

Rated voltage 250 V

##### Electric current

Rated current 13 A

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Colour Anthracite

RAL code 7021

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

##### Dimensions

Height 71 mm

Width 71 mm

Built-in depth flush-mounted boxes 40 mm

##### Installation, mounting

Mounting on Flush mounting

##### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

##### Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

##### Accessories

Has labelling field No

##### Capacity

Number of modules 1

##### Safety

With enhanced contact protection No

Impact resistance IK IK02

Ingress Protection (IP) class IP20

##### Functions

With orientation lighting No

With function lighting No

##### Texts

Imprint Without imprint

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With screw terminals

##### Suitable for

Q.x / S.x/B.x

---

**Sustainability**

---

Halogen free	Yes
RoHS conform	Yes

---