

# Product Datasheet

## 53420219



53420219



Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

### Technical Features

#### Electric current

Rated current	13 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

#### Dimensions

Height	71 mm
Width	71 mm
Built-in depth flush-mounted boxes	40 mm

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	1
-------------------	---

#### Controls and indicators

Type of lighting for the installation devices	Integrated operating control light
---	------------------------------------

#### Safety

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

#### Functions

With orientation lighting	No
With function lighting	No

#### Texts

Imprint	Without imprint
Cover	Central cover plate

Texts	
Protection	Enhanced contact protection
Type of connection	With screw terminals

Suitable for	
Q.x / S.x/B.x	

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes