



53420219



Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 13 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white  
RAL code 9010  
Surface finish Glossy  
Material Thermoplastic  
Treatment Untreated

**Dimensions**

Height 71 mm  
Width 71 mm  
Built-in depth flush-mounted boxes 40 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal  
Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet British Standard  
Rotated central insert No  
With hinged lid No  
With round protective earth pin No  
With signal lamp No  
With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Controls and indicators**

Type of lighting for the installation devices Integrated operating control light

**Safety**

With enhanced contact protection No  
Impact resistance IK IK02  
Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No  
With function lighting No

**Identification**

With imprint No

---

**Texts**

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes