



WGCXT1RJ6EG

**RJ45 outlet cat6 (1mod);eg**

**Technical Features**

**Frequency**

Transmission bandwidth 0-250 MHz

**Equipment**

With transparent label holder No

Number of outputs 1

**Use conditions**

Operating temperature -20 - 45 °C

**Equipment**

With hinged lid No

**Materials**

Colour Gold

**Connection**

Connector/plug type RJ45

**Materials**

Material Polycarbonate (PC)

**Safety**

Ingress Protection (IP) class IP20

**Voltage**

Rated voltage 0 V

**Electric current**

Rated current 0 A

**Dimensions**

Built-in depth 27 mm

**Sustainability**

RoHS conform Yes