



WNC132B

**cubyko Double vertical socket 2P+E screwless wall mounted white IP55**

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Pure white
RAL code	9010
Surface finish	Satin finish
Material	Polypropylene (PP)
Treatment	Varnished

**Dimensions**

Height	75 mm
Width	75 mm
Depth	22.80 mm

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Connectivity**

Type of connection	Plug-in connection
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	French norm NF
Rotated central insert	No
With hinged lid	Yes
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Cover, door**

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

**Capacity**

Number of modules	4
-------------------	---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55

**Functions**

With orientation lighting	No
---------------------------	----

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	For covering of socket outlets
Protection	Without protective screen

**Suitable for**

cubyko	
--------	--

---

**Sustainability**

---

Halogen free	Yes
RoHS conform	Yes

---