



FWB53

FWB encl.,univers,5rows 180 mod cl.II IP44,plain door,800x800x161mm,brass term.

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	15
Number of rows	5
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	180
-------------------	-----

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	800 mm
Width	800 mm
Depth	165 mm

Cover, door

Number of cabinet doors	2
-------------------------	---

Dimensions

Built-in depth	161 mm
----------------	--------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	36
-----------------------	----

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connection

Number of conduit inlets	12
--------------------------	----

Connectivity

Mounting type	Surface mounting
---------------	------------------

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK09

Safety

Ingress Protection (IP) class	IP44
Locking type	Bar lock Without lock

Sustainability

RoHS conform	Yes
--------------	-----