



K96L

Busbar terminal 16mm<sup>2</sup>-120mm<sup>2</sup>, for 12x10mm busbars, for copper conductors

**Technical Features**

**Connection**

Cross-section flexible conductor	16 - 120 mm <sup>2</sup>
Cross-section rigid conductor	16 - 120 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	22 - 22 Nm
---------------------------	------------

**Dimensions**

Width/thickness busbar	10 - 10 mm
Height	29.50 mm
Width	23.50 mm
Depth	58 mm

**Electric current**

Rated current	440 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----