



K96W

Busbar terminal 16mm²-120mm², for 12x5mm busbars, for copper conductors

Technical Features

Connection

Cross-section flexible conductor	16 - 120 mm ²
Cross-section rigid conductor	16 - 120 mm ²

Installation, mounting

Nominal tightening torque	22 - 22 Nm
---------------------------	------------

Dimensions

Width/thickness busbar	5 - 5 mm
Width	23.50 mm
Depth	58 mm

Electric current

Rated current	440 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----